

# -80°C temperature intelligent sensor



Temperature intelligent sensors from -80°C, thin cable standard cable length 50 cm, different probes available, cannot be switched; for longer cable length purchase ZED extensions. This sensor is already connected, included in the price, on the ZED IT T.-80.

Intelligent sensors are much more than simple sensors. The idea of an intelligent sensor is based on the fact that its parameters (serial number, type etc.) and the calibration data are stored electronically in a circuit installed on its cable or inside the connector. In this way you can connect to a reading device or directly to your PC, several intelligent sensors of different kind and they will all be recognized for what they are and what they are able to read, along with their calibration data. The sensor sends to the device (PC or data logger) a digital calibrated data.

The main feature of the intelligent sensors, used in the Syrinx system and connected to the ZED modules, is the **recalibration procedure: easy, quick and not expensive**. You won't need to remove the ZEDs from their position. You won't need to send the sensors to Tecnosoft for recalibration and therefore remain without monitoring. Before calibration expires order the recalibration service for intelligent sensors. You will receive new sensors to replace the expiring ones that will be sent back to Tecnosoft later on.

All intelligent sensors come with an **Accredia** (NIST equivalent) **traceable calibration certificate included**.

## Main features

- Standard cable length (50 cm) available but different rigid stainless steel probes: 30 or 80 mm, rounded or pointed
- Using the extensions it is possible to extend the cable length
- Possibility to switch sensors and devices with no calibration loss

## Plus

- Easy recalibration: no need to uninstall the whole device for recalibration (sensor and unit), just disconnect the uncalibrated sensor and connect the calibrated one
- Time saving: you never lose a single minute of monitoring, since you receive the new calibrated sensor BEFORE unplugging the old one (that will be sent back to us)
- Easy to use: no configuration needed. The system recognizes automatically the sensors connected

## The system

Intelligent sensors work with the Syrinx system and the FridgeLog Z software:

- ZED with one or two Intelligent Sensors
- FridgeLog Z software
- EAP receiver
- Syrinx collector



## Applications



Environment



Warehouses



Pharmaceutical



Healthcare



Food & Beverages



Medical



Laboratories



Logistic&Transport



Industrial



Cold Chain

## Accessories

- ZED IT cable extensions
- FridgeLog Z
- Syrinx Mini
- Syrinx L
- Syrinx desktop
- Syrinx software

## Technical specifications

Intelligent sensor dimensions	Cable 500 l X 2 Ø (mm) - Probe 30 or 80 l X 4 Ø (mm) pointed or rounded
Sensor temperature range	-80 °C ÷ +20 °C
Extra calibration points (temperature)	Within standard calibration range
Standard calibration points (temperature)	-80/-40/0/20°C
Temperature resolution	0,03 °C
Temperature accuracy	± 0,5 °C (within the calibration range)